
DIN 580

Eye bolts

With flange and groove | round ring

Stainless steel A2 | Cr(VI)-free | Metric thread





Diameter	d ₁	d_2			d_3			d ₄
(d)	nominal size	nominal size	min.	max.	nominal size	min.	max.	
M8	M 8	20	19.5	20.9	36	35.5	37.1	20
M10	M 10	25	24.5	25.9	45	44.5	46.1	25
M12	M 12	30	29.5	30.9	54	53.5	55.1	30
M16	M 16	35	34.5	36.1	63	62.5	64.1	35
M20	M 20	40	39.5	41.1	72	71.5	73.1	40
M24	M 24	50	49.4	51.2	90	89.4	91.2	50

Diameter	е			f	h			Pitch
(d)	nominal size	max.	min.	max.	nominal size	min.	max.	(P)
M8	6	6.9	5.5	2.5	36	35.5	37.1	1.25
M10	8	8.9	7.5	3.0	45	44.5	46.1	1.50
M12	10	10.9	9.5	3.5	53	52.5	54.1	1.75
M16	12	12.9	11.5	4.0	62	61.5	63.1	2.00
M20	14	14.9	13.5	5.0	71	70.5	72.1	2.50
M24	18	19.1	17.5	6.0	90	89.4	91.2	3.00

Length (I)					
nominal size	min.	max.			
13.0	12.65	13.35			
17.0	16.65	17.35			
20.5	20.08	20.92			
27.0	26.58	27.42			
30.0	29.58	30.42			
36.0	35.50	36.50			
36.0	35.50	36.50			

All technical data refer to the measure mm

DIN 580

Eye bolts

With flange and groove | round ring

Stainless steel A2 | Cr(VI)-free | Metric thread



• Combinations available in the eShop | Other sizes on request