
## **DIN 7981 C** similar to ISO 7049

## **Tapping screws**

Button head | cross-slot phillips | form C with cone point

Stainless steel A2 | Cr(VI)-free | Thread type ST (sheet metal)

Further information: DIN-standard has been withdrawn | changed head measurements with ISO norm





Diameter	а	d <sub>k</sub>		ŀ	<	rf	r	Pitch	Tool
(d)	max.	min.	max.	min.	max.		max.	(P)	size
2.2	0.8	3.90	4.2	1.55	1.80	3.4	0.3	0.8	Т8
2.9	1.1	5.30	5.6	1.95	2.20	4.4	0.4	1.1	T10
3.5	1.3	6.54	6.9	2.35	2.60	5.4	0.5	1.3	T15
4.2	1.4	7.84	8.2	2.75	3.05	6.2	0.6	1.4	T20
4.8	1.6	9.14	9.5	3.25	3.55	7.2	0.7	1.6	T25
5.5	1.8	10.37	10.8	3.65	3.95	8.2	0.8	1.8	T27
6.3	1.8	12.07	12.5	4.25	4.55	9.5	0.9	1.8	T30

Length (I)								
nominal size	min.	max.						
9.5	8.7	10.3						
13.0	12.2	13.8						
16.0	15.2	16.8						
19.0	18.2	19.8						
22.0	21.2	22.8						
25.0	24.2	25.8						

Length (I)								
nominal size	min.	max.						
32.0	30.7	33.3						
38.0	36.7	39.3						
45.0	43.7	46.3						
50.0	48.7	51.3						
60.0	58.7	61.3						


## All technical data refer to the measure mm

**DIN 7981 C** similar to ISO 7049

## **Tapping screws**

Button head | cross-slot phillips | form C with cone point

Stainless steel A2 | Cr(VI)-free | Thread type ST (sheet metal)



• Combinations available in the eShop | Other sizes on request