

DIN 7985 similar to ISO 7045

Pan head screws

Cross-slot pozidriv

Steel 4.8 | zinc-plated | Cr(VI)-free | Metric thread

Further information: DIN-standard has been withdrawn | changed head height

Diameter (d)	a	d _a	d _k		k			rf	r	Pitch (P)	v	Tool size
	max.	max.	min.	max.	nominal size	min.	max.	max.	max.			
M2	0.8	2.6	3.70	4	1.6	1.48	1.72	4	0.10	0.40	1.1	Z1
M2.5	0.9	3.1	4.70	5	2.0	1.88	2.12	5	0.10	0.45	1.3	Z1
M3	1.0	3.6	5.70	6	2.4	2.28	2.52	6	0.10	0.50	1.6	Z1
M4	1.4	4.7	7.64	8	3.1	2.95	3.25	8	0.20	0.70	2.0	Z2
M5	1.6	5.7	9.64	10	3.8	3.65	3.95	10	0.20	0.80	2.5	Z2
M6	2.0	6.8	11.57	12	4.6	4.45	4.75	12	0.25	1.00	3.0	Z3
M8	2.5	9.2	15.57	16	6.0	5.85	6.15	16	0.40	1.25	3.7	Z4

nominal size	Length (l)	
	min.	max.
4	3.75	4.25
5	4.75	5.25
6	5.75	6.25
8	7.70	8.30
10	9.70	10.30
12	11.65	12.35
14	13.65	14.35
16	15.65	16.35

nominal size	Length (l)	
	min.	max.
20	19.60	20.40
25	24.60	25.40
30	29.60	30.40
35	34.50	35.50
40	39.50	40.50

Diameter (d)	Length (l)												
	4	5	6	8	10	12	14	16	20	25	30	35	40
M2				●									
M2.5	●	●	●					●					
M3	●		●		●	●	●	●	●	●			●
M4				●	●	●			●	●	●	●	
M5					●	●			●	●			
M6					●			●					
M8									●				

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

