

E 1423

EJOT®-PT screws

Countersunk head | cross-slot phillips

Stainless steel A2 | Cr(VI)-free | Self-tapping thread

Further information: For further information and CAD-files please follow the link to the EJOT-homepage:

<http://www.ejot.com/industry>

Diameter (d)	c max.	d ₁ nominal size	r nominal size	Pitch (P)	t max.	t min.	Tool size
2.5	0.55	2.5	1	1.12	1	0.8	T8
3	0.55	3	1.2	1.34	1	0.8	T8

Length (l) nominal size
8
10
14

Diameter (d)	Length (l)		
	8	10	14
2.5	●	●	
3	●		●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

