E 5451

EJOT®-Delta PT-screws


Raised countersunk head with pressed-on washer | torx plus /autosert drive


Stainless steel A2 | Cr(VI)-free | Self-tapping thread

Further information: For further information and CAD-files please follow the link to the EJOT-homepage:

http://www.ejot.com/industry







Diameter	d ₁	d_2	k	s	Pitch		Tool	
(d)	nominal size	nominal size	nominal size	nominal size	(P)	max.	min.	size
2	4.5	1.36	1.6	0.6	0.78	0.85	0.65	T6
2.2	5	1.51	1.6	0.6	0.85	0.85	0.65	T6
2.5	5.5	1.72	1.9	0.7	0.95	1.00	0.80	T8
3	6.5	2.09	2.3	0.8	1.12	1.30	1.00	T10
3.5	7.5	2.45	2.7	0.9	1.29	1.50	1.10	T15
4	9	2.81	3.1	1.0	1.46	1.80	1.40	T20
5	11	3.53	3.5	1.2	1.80	1.90	1.50	T25
6	13.5	4.26	4.2	1.4	2.14	2.40	1.90	T30

Length (I)	
nominal size	
4.5	
6.0	
7.0	
8.0	
10.0	
12.0	

Length (I)
nominal size
14.0
15.0
16.0
20.0
25.0
30.0

All technical data refer to the measure mm

E 5451

EJOT®-Delta PT-screws

Raised countersunk head with pressed-on washer | torx plus /autosert drive

Stainless steel A2 | Cr(VI)-free | Self-tapping thread

Diameter	Length (l)											
(d)	4.5	6	7	8	10	12	14	15	16	20	25	30
2		•	•	•								
2.2												
2.5								lacktriangle				
3						•						
3.5						•	•			•		
4												
5												
6												

• Combinations available in the eShop | Other sizes on request