
Advantages:

- Suitable for thermoplastic parts
- Especially designed for ultrasonic installation
- Screw-locked and low-tension anchoring
- High pull-out values
- Type 0730 can be installed from both sides. Advantages for automatic feed, since no directional orientation is required





Diameter	Article number	d ₃	Length (I)	а	l ₂		Outer	L
(d)		nominal size	nominal size	min.		D1	diameter (d2)	min.
M 2	07341020046	5	4.0	2.0	0.6	5.2	3.6	4.5
M 2.5	07341250064	6	5.8	2.3	0.6	6.2	4.6	6.5
М3	07341030064	6	5.8	2.3	0.6	6.2	4.6	6.5
M 4	07341040009	8	8.2	2.5	0.8	8.2	6.3	9.0
M 5	07341050105	8.5	9.5	2.7	1.0	8.7	7	10.5
M 6	07341060137	10	12.7	3.0	1.0	10.2	8.6	14.0
M 8	07341080137	12	12.7	3.5	1.0	12.2	10.2	14.0