


# QUICKSERT® Expansion

Brass | Type 1230 | standard

**Advantages:**

- No tapping
- Quick, cost-effective installation
- Chipping-free installation in smooth mounting holes
- High-strength threads in light metals
- High-strength threads in thermoplastic and thermoset components\*\* after moulding of components
- Suitable for one-sided accessibility of the installation point
- For screwed connections that can be detached as often as required
- For installation on finished surfaces

\*\* Particularly test this insert for suitability for plastics susceptible to stress cracks (e.g. PC, PPO).



Diameter (d)	a nominal size	Length (l) nominal size	l <sub>1</sub>	Outer diameter (d2)	L min.	L2 min.
M3	2.0	8.0	4.8	5.5	8.8	4.8
M5	2.5	13.5	8.2	7.5	15.2	8.2
M6	3.0	16.0	9.8	9	18.8	9.8
M8	4.0	19.0	11.5	12	21.0	11.5

All technical data refer to the measure mm

