

RIVKLE® BRK 01 Kit

RIVKLE® kit including RIVKLE® BRK 01 hand-held setting pliers

Delivery scope:

- 1 RIVKLE® BRK 01 hand-held setting pliers
- 4 threaded mandrels and 4 anvils (M3, M4, M5, M6)
- 50 blind rivet nuts each, small countersunk head, steel (M3, M4, M5, M6)
- Practical case for storage and transport
- Operating instructions

Function:

Screwing and unscrewing of the RIVKLE® blind rivet nut using a knurled nut. Setting is performed through the lever action of the hand-held tool.

Technical information can be found on the last page.



Diameter (d)	Weight g
M3 - M6	600



Head diameter
Overall length
Thread size



Grip range
 Defines the range of total thickness of the customers part (even if it consists of more than one layer)



Hole geometry
 If round → diameter
 If hexagonal → width across flats




Head projection after setting
 Variable according to the application (setting load, material substrate, etc.)


Blind side projection after installation
 Defines the clearance needed on the blind side (cannot be used for quality control)

Setting stroke
 Difference of total length before and after installation

RIVKLE® Nut



RIVKLE® Stud



- RIVKLE®
- Mandrel*
- Customers part
- Anvil*
- Counter nut
- Setting tool

in accordance to chosen RIVKLE®

All technical data refer to the measure mm

