


B 251
RIPP LOCK® self-locking screws

Cylinder head with flange and tothing | hexagon socket

Steel | zinc-plated | Cr(VI)-free | Metric thread

Further information: Strength class 100



Diameter (d)	a		b		d ₂		d _c		d _k	
	max.	nominal size	min.	max.	min.	max.	min.	max.	min.	max.
M 5	2.40	22	5.7	5.9	10.0	11.0	8.5	9		
M 6	3.00	24	6.8	7.0	12.5	13.5	10.0	11		
M 8	3.75	28	9.2	9.4	16.0	17.0	13.0	14		
M 10	4.50	32	11.2	11.5	18.5	19.5	16.0	17		
M 12	5.25	36	13.7	14.0	21.5	22.5	18.0	19		

Diameter (d)	k		e	s		Pitch (P)	Tool size
	min.	max.		min.	max.		
M 5	4.82	5	4.58	4	4.02	0.80	SW 4
M 6	5.70	6	5.72	5	5.02	1.00	SW 5
M 8	7.64	8	6.86	6	6.02	1.25	SW 6
M 10	9.64	10	9.15	8	8.02	1.50	SW 8
M 12	11.57	12	11.43	10	10.02	1.75	SW 10

nominal size	Length (l)	
	min.	max.
10	9.71	10.29
12	11.65	12.35
16	15.65	16.35
20	19.58	20.42
25	24.58	25.42
30	29.58	30.42

nominal size	Length (l)	
	min.	max.
35	34.50	35.50
40	39.50	40.50
45	44.50	45.50
50	49.50	50.50

All technical data refer to the measure mm



B 251
RIPP LOCK® self-locking screws

Cylinder head with flange and tothing | hexagon socket

Steel | zinc-plated | Cr(VI)-free | Metric thread

Diameter (d)	Length (l)									
	10	12	16	20	25	30	35	40	45	50
M 5	●	●	●	●						
M 6		●	●	●	●	●				
M 8			●	●	●	●		●		
M 10				●	●	●	●	●		
M 12						●	●	●	●	●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

