


DIN 938
Studs

Threaded end $\approx 1 d$

Stainless steel A2 | Cr(VI)-free | Metric thread

Einschraubende

Mutterende



Diameter (d)	b			b ₁ nominal size	d _s		z ₂	z ₁
	l up to 125	l up to 200	l longer than 200		min.	max.		
M 5	16	22	–	5	4.82	5	1.00	2
M 6	18	24	–	6	5.82	6	1.25	2.5
M 8	22	28	–	8	7.78	8	1.60	3.2
M 10	26	32	45	10	9.78	10	1.90	3.8
M 12	30	36	49	12	11.73	12	2.20	4.3
M 16	38	44	57	16	15.73	16	2.50	5
M 20	46	52	65	20	19.67	20	3.20	6.3
M 24	54	60	73	24	23.67	24	3.80	7.5
M 27	60	66	79	25	26.67	27	3.80	7.5
M 30	66	72	85	30	29.67	30	4.50	9

nominal size	Length (l)	
	min.	max.
16	15.65	16.35
20	19.58	20.42
25	24.58	25.42
30	29.58	30.42
35	34.50	35.50
40	39.50	40.50
45	44.50	45.50
50	49.50	50.50

nominal size	Length (l)	
	min.	max.
55	54.40	55.60
60	59.40	60.60
65	64.40	65.60
70	69.40	70.60
75	74.40	75.60
80	79.40	80.60
85	84.30	85.70
90	89.30	90.70

nominal size	Length (l)	
	min.	max.
95	94.30	95.70
100	99.30	100.70
110	109.30	110.70
120	119.30	120.70

All technical data refer to the measure mm



DIN 938
Studs

Threaded end $\approx 1 d$

Stainless steel A2 | Cr(VI)-free | Metric thread

Diameter (d)	Length (l)																			
	16	20	25	30	35	40	45	50	55	60	65	70	75	80	85	90	95	100	110	120
M 5	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M 6	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M 8	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M 10		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M 12		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M 16				●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M 20						●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M 24							●	●	●	●	●	●	●	●	●	●	●	●	●	●
M 27										●		●		●		●		●	●	●
M 30										●		●		●		●		●	●	●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

