

DIN 938
Studs


Threaded end $\approx 1 d$

Steel 5.8 | zinc-plated | Cr(VI)-free | Metric thread



Einschraubende

Mutterende



Diameter (d)	b			b ₁ nominal size	d _s		Pitch (P)	z ₂	z ₁
	l up to 125	l up to 200	l longer than 200		min.	max.			
M8	22	28	–	8	7.78	8	1.25	1.6	3.2
M10	26	32	45	10	9.78	10	1.50	1.9	3.8
M12	30	36	49	12	11.73	12	1.75	2.2	4.3
M16	38	44	57	16	15.73	16	2.00	2.5	5
M20	46	52	65	20	19.67	20	2.50	3.2	6.3

nominal size	Length (l)	
	min.	max.
30	29.58	30.42
35	34.50	35.50
40	39.50	40.50
50	49.50	50.50
55	54.40	55.60
60	59.40	60.60

nominal size	Length (l)	
	min.	max.
65	64.40	65.60
70	69.40	70.60
80	79.40	80.60

Diameter (d)	Length (l)								
	30	35	40	50	55	60	65	70	80
M8	●		●						
M10		●	●	●					
M12				●					
M16					●	●	●		
M20						●	●	●	●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

