


ISO 4032 similar to DIN 934

Hexagon nuts

Steel 5 - 2 | bright | Cr(VI)-free | Metric thread

Further information: ISO-standard has been withdrawn | changed spanner widths for M10, M12, M14 and M22 | changed head height | the fine thread has been transferred to ISO 8673



Diameter (d)	d _a		d _w	e	m		s		Pitch (P)	Tool size
	min.	max.			min.	max.	min.	max.		
M 6	6	6.75	8.9	11.05	4.90	5.2	9.78	10	1.00	SW 10
M 8	8	8.75	11.6	14.38	6.44	6.8	12.73	13	1.25	SW 13
M 10	10	10.80	14.6	17.77	8.04	8.4	15.73	16	1.50	SW 16
M 12	12	13.00	16.6	20.03	10.37	10.8	17.73	18	1.75	SW 18
M 14	14	15.10	19.6	23.36	12.10	12.8	20.67	21	2.00	SW 21
M 16	16	17.30	22.5	26.75	14.10	14.8	23.67	24	2.00	SW 24
M 18	18	19.50	24.9	29.56	15.10	15.8	26.16	27	2.50	SW 27
M 20	20	21.60	27.7	32.95	16.90	18.0	29.16	30	2.50	SW 30
M 22	22	23.70	31.4	37.29	18.10	19.4	33.00	34	2.50	SW 34
M 24	24	25.90	33.3	39.55	20.20	21.5	35.00	36	3.00	SW 36
M 27	27	29.10	38.0	45.20	22.50	23.8	40.00	41	3.00	SW 41
M 30	30	32.40	42.8	50.85	24.30	25.6	45.00	46	3.50	SW 46
M 33	33	35.60	46.6	55.37	27.40	28.7	49.00	50	3.50	SW 50
M 36	36	38.90	51.1	60.79	29.40	31.0	53.80	55	4.00	SW 55
M 39	39	42.10	55.9	66.44	31.80	33.4	58.80	60	4.00	SW 60
M 42	42	45.40	60.0	71.30	32.40	34.0	63.10	65	4.50	SW 65
M 45	45	48.60	64.7	76.95	34.40	36.0	68.10	70	4.50	SW 70

All technical data refer to the measure mm

