All technical data refer to the measure mm

RIVKLE® Standard blind rivet nuts


Steel zinc-plated | Flat head | Plain | Cylindrical | Closed


Note: Thread according to ISO 6h (ISO 68-1) - Corrosion resistance 400 h salt spray | Cr(VI)-free

Technical information can be found on the last page.




Diameter	Article number	Drilling diameter d		E	L ₂	е		Length (I)	
(d)		nominal size	В	nominal size		min.	max.	nominal size	S
М3	23321030030	5	7.5	1	9.2	1.5	3.0	14.30	S = 4.1 - e
M 4	23321040020	6	9.0	1	10.4	1.0	2.0	15.25	S = 5.2 - e
	23321040040				10.4	2.0	4.0	16.75	S = 5.6 - e
	23321040060				10.3	4.0	6.0	18.80	S = 7.6 - e
M 5	23321050030	7	10.0	1	14.0	0.5	3.0	19.70	S = 5.0 - e
	23321050055				14.0	3.0	5.5	22.70	S = 7.5 - e
	23321050080				15.1	5.5	8.0	25.70	S = 9.6 - e
M 6	23321060030	9	13.0	1.5	16.3	0.5	3.0	22.70	S = 4.9 - e
	23321060055				17.0	3.0	5.5	25.70	S = 7.7 - e
	23321060080				17.0	5.5	8.0	28.70	S = 10.2 - e
M 8	23321080030	11	16.0	1.5	19.0	0.5	3.0	25.70	S = 5.7 - e
	23321080055				19.0	3.0	5.5	28.70	S = 8.2 - e
	23321080080				19.0	5.5	8.0	31.70	S = 10.7 - e
	23321080105				20.4	8.0	10.5	34.80	S = 12.9 - e
M 10	23321100035	13	19.0	2	25.0	1.0	3.5	32.70	S = 6.5 - e
	23321100060				25.4	3.5	6.0	35.80	S = 8.4 - e
	23321100085				25.6	6.0	8.5	38.80	S = 11.2 - e
M 12	23321120040	16	23.0	2	29.6	1.0	4.0	38.80	S = 7.2 - e
	23321120070				29.4	4.0	7.0	41.80	S = 10.4 - e






Grip range

Defines the range of total thickness of the customers part (even if it consists of more than one layer)



Hole geometry

If round -> diameter
If hexagonal -> wigth across flats





in accordance to chosen RIVKLE®

