

## RIVKLE® HRT Blind rivet nuts

Steel zinc-plated | Flat head | Hexagonal | Hexagonal | Open

Note: Thread according to ISO 6h (ISO 68-1) -Equivalent nut class 10 or 12 (compatible screw class 10,9 or 12,9)

Technical information can be found on the last page.



Diameter (d)	Drilling diameter d nominal size	B	E nominal size	L <sub>2</sub>	e		Length (l) nominal size	S
					min.	max.		
M 8	11	17	1.5	16.0	3	6.0	26.6	S = 9.6 - e
		20		17.5	1	3.5	27.0	S = 8.7 - e
M 10	13	24	2	18.0	2	5.0	28.5	S = 9.5 - e
		27		22.0	1	4.0	33.0	S = 10.5 - e

All technical data refer to the measure mm





**Head diameter**  
**Overall length**  
**Thread size**



**Grip range**  
 Defines the range of total thickness of the customers part (even if it consists of more than one layer)



**Hole geometry**  
 If round → diameter  
 If hexagonal → wigth across flats




**Head projection after setting**  
 Variable according to the application (setting load, material substrate, etc.)


**Blind side projection after installation**  
 Defines the clearance needed on the blind side (cannot be used for quality control)

**Setting stroke**  
 Difference of total length before and after installation

**RIVKLE® Nut**



**RIVKLE® Stud**



- RIVKLE®
- Mandrel\*
- Customers part
- Anvil\*
- Counter nut
- Setting tool

\*in accordance to chosen RIVKLE®\*

All technical data refer to the measure mm

